SAMCEN

Ideas For Communication

Fully Digital Voting Unit SCS-6190C SCS-6190D



Products picture



Features

New process, high gloss surface, anti-scratch, anti-oxidation, fade-proof, rub resistance, easy to clean, feel relieved to buy and feel at ease to employ.

- 1. Novel appearance design and exquisite technical process enable the cabinet rank in the first line of international superior conference system.
- 2. 5 keys for voting and electing.
- 3. With the function of sign in.
- 4. Working with Samcen software for various kinds of voting.
- 5. First choice for large-scale & important conferences, such as International Conferences, Summits, Standing Committee.
 6. With voice control ability the voice can turn on microphone, it does not need to press the microphone button by hand.
- 7. Each microphone unit connects "hand in hand", avoid the miscellaneous of circuit, easy to install and maintain. It is also benefit to add/cut down the microphone units.
- 8. Perfect sound quality, feedback eliminator function. When microphone is turned on, the built-in loudspeaker closes automatically to avoid feedback.
- 9. Double microphones input(with clip-on microphone interface). 10. Gooseneck condenser microphone supports "PnP" (Plug-and-Play), speaking with red ring indicator.
- 11. Microphones power controllable by main unit, the input voltage is 24V. It's safety voltage.
- 12.LCD display shows congressional information and status of equipment.
- 13. Working with the control system to realize the function of camera auto-tracking.
- 14. Chairman unit has priority to speak, it can close/ temporarily muting the delegate unit.
- 15. Super powers of anti-electromagnetic and mobile phone interference.
- 16. Microphone rods can be taken down during the recess, easy to maintain.
- 17. Humanization design. There is different length MIC rods to choose, it is suitable for different height attendances.
- 18. Without software, chairman can launch a simple vote:
- a) Sign in, elect 1/3, elect 1/5, vote and score, the result will be displayed on LCD screen.
- 19. With SAMCEN professional software:
- a) Sign in, elect 1/3, elect 1/5, vote and score.
- b) The list of candidate and attendance, result of sign in, the bill title and details display on the main screen and the second screen.
- c) Check the problem unit and find out who do not sign in.
- Display the result of voting in the form of data or chart and print

Specifications

Model	SCS-6190C/D
Power supply	DC24V supplied by the control host
Intercommunication	DIN 8-pole
Power consumption	3W
Loudspeaker power	1.2W
Transducer type	Electret condenser
Directional pattern	Cardioid
SNR	> 80dB
Crosstalk attenuation at 1k Hz	> 80dB
Distortion	<0.10%
Frequency response	6 0~12KHz
Equivalent noise	≈20dB SPL
Maximum SPL	105dB(3% threshold)
Sensitivity	-22dBv/Pa

Project













Connection diagram

